



Hach Orbisphere 3650/3655 Selective Oxygen Measurement

Applications

- Drinking water
- Pure water applications
- Food and beverage



Ideal for Harsh Environments

The Orbisphere 3650 offers a robust portable system solution for oxygen measurement. The compact stainless steel construction is designed for the harsh environment of breweries, but it is also perfectly adapted for laboratory or verification purposes in other beverage applications. In addition, the 3650 can be used across a wide range of applications in the power generation, electronics and life sciences industries.

Designed for use with the Orbisphere GA2400/GA2800 high quality oxygen sensor, these instruments provide fast, accurate and repeatable measurements in both the dissolved and gaseous phase, at line or in the laboratory. For low level applications, the specially configured Orbisphere 3655 measures to 0.1 ppb oxygen.

Simple Operation and Data Management

The Orbisphere 3650 inlet tube is connected to a sample point or to a piercing device by a simple connector, making it quick and easy to install. The sample flows over the sensor membrane in the flow chamber, with an output valve controlling the sample's flow rate.

Each instrument comes with a Windows software package that enables the user to analyse up to 500 stored measurements and to configure the instrument. Using the RS232 connection, stored measurements can be simply downloaded to a PC for analysis.

Simple Maintenance

The use of the Orbisphere GA2400/GA2800 sensor with this portable instrument allows for very quick cleaning with nothing more than tap water and requires no technical skills. The sensor refurbishment (typically every 6 months) takes only 3 minutes with a pre-mounted membrane cartridge and electrolyte, eliminating any risk of incorrect membrane positioning.

The Orbisphere 3650 uses two C-type, NiMH or alkaline batteries. Changing the batteries is quick and easy; stored measurements are not lost if batteries go flat or are being changed.

Easy Calibration

Calibration after each sensor refurbishment is recommended. A traceable and simple calibration can be done directly in air by measuring its oxygen content with the use of the built-in pressure sensor and the automatic software calculation. Alternatively, the calibration can be performed against a liquid or gaseous sample of known concentration by simply entering the gas concentration via the keyboard.

Technical Data*

Sample & Instrument	
Sample temperature	-5 °C - 60 °C (23 °F - 140 °F)
Sample pressure	Max. 10 bar (145 psi)
Power supply	Two C-type cells, NiCd or alkaline, each 26 x 50 mm, 2.4 - 3 Volt total
Battery life	40 hours continuous use
Data storage	500 data
Compliance certifications	CE: EN61010-1: LVD Directive ISO9001/EN29001
Enclosure waterproof rating	IP65 / NEMA4
Operating temperature range	-5 °C - 100 °C (23 °F - 212 °F)
Temperature compensation	-5 °C - 60 °C (23 °F - 140 °F)
Dimensions (H x W x D)	150 mm x 115 mm x 220 mm
Weight	2.4 kg

Configurations				
Model	3650/111	3650/112	3650/113	3655/111
Display Units	ppm/ppb or ppm only	% or ppm	% (gaseous) or ppm (liquid)	ppm/ppb or ppm only
Display resolution	1 ppb or 0.001 ppm	1 ppm	0.001 ppm or 0.001%	0.1 ppb or 0.001 ppm

Measurement				
Membrane	2952A	2956A	2958A	29552A
Response time	38 s	7.2 s	9.5 s	90 s
Measuring range	O ₂ (dissolved): 1 ppb - 80 ppm O ₂ (gaseous): 5 Pa - 200 kPa	O ₂ (dissolved): 0.1 ppb - 20 ppm O ₂ (gaseous): 0.25 Pa - 50 kPa	O ₂ (dissolved): 1 ppb - 40 ppm O ₂ (gaseous): 2 Pa - 100 kPa	O ₂ (dissolved): 2 ppb - 80 ppm O ₂ (gaseous): 5 Pa - 200 kPa
Flow rate	Min. liquid: 50 mL/min Min. gaseous: 0.1 - 3 L/min	Min. liquid: 180 mL/min Min. gaseous: 0.1 - 3 L/min	Min. liquid: 120 mL/min Min. gaseous: 0.1 - 3 L/min	Min. liquid: 50 mL/min Min. gaseous: 0.1 - 3 L/min
Accuracy	The greater of ±1% of reading or ±2 ppb or ±5 Pa	The greater of ±1% of reading or ±0.1 ppb (3655)/±1 ppb (3650) or ±0.25 Pa	The greater of ±1% of reading or ±1 ppb or ±2 Pa	The greater of ±1% of reading or ±2 ppb or ±5 Pa

Note: Instruments are user-configured for a particular membrane, depending on the application. This determines the display resolution and measurement limits.

*Subject to change without notice.

Order Information

Instruments

3650/111	Orbisphere 3650/111 Portable Analyser, Dissolved Oxygen (O ₂), units: ppm/ppb or ppm only
3650/112	Orbisphere 3650/112 Portable Analyser, Gas Phase Oxygen (O ₂), units: % or ppm
3650/113	Orbisphere 3650/113 Portable Analyser, Gaseous or Dissolved Oxygen (O ₂), units: % (gaseous) or ppm (liquid)
3655/111	Orbisphere 3655/111 Portable Analyser, Dissolved Oxygen (O ₂), high resolution, units: ppm/ppb or ppm only
GA2400-S00	Orbisphere GA2400 Stainless Steel Oxygen Sensor (EC), 40 bar, EPDM O-rings

Accessories/Options

32007D	Flow chamber in Delrin for power logger (3655), 1 m tubing
32051A	Adapter for 32007D, incl. one 6 mm and one 8 mm rubber sealing gasket
2952A-A	Recharge kit of 4 pre-filled cartridges with premounted 2952A membranes
2956A-A	Recharge kit of 4 pre-filled cartridges with premounted 2956A membranes
2958A-A	Recharge kit of 4 pre-filled cartridges with premounted 2958A membranes
29552A-A	Recharge kit of 4 pre-filled cartridges with premounted 29552A membranes
32687	Windows Software 32689 plus communications cable for 3650 & 3655 instruments
32751	Battery recharger with pack of two rechargeable NiCd batteries (Europe only)



With Hach Service, you have a global partner who understands your needs and cares about delivering timely, high-quality service you can trust. Our Service Team brings unique expertise to help you maximise instrument uptime, ensure data integrity, maintain operational stability, and reduce compliance risk.



Distribuidor autorizado de HACH en:

 Argentina

Tel: (+54 11) 5352 2500

Email: info@dastecsrl.com.ar

Web: www.dastecsrl.com.ar

 Uruguay www.dastecsrl.com.uy

 Paraguay www.dastecsrl.com.py



www.hach.com